

# MINOLTA DUOFIT-S

## 1968



Serial Nr.: no  
Minolta Code: unknown

### Characteristics and Functions

The Minolta Duofit-S has a white plastic body, and can be used with bulb type AG-1, AG-1B and AG-3B bulbs. On the front side there is the metal parabola with the seat where to insert the foot of the bulb; on the right side comes out the gray sync cable for connection with the camera. On the back there are: the table of apertures to be set on the camera according to the sensitivity of the film used and the shooting distance, the large orange Test button and the white

plastic button which, when pressed, allows you to eject the bulb used. As shown in the table, the shutter speed must be 1/30". On cameras with guide numbers set the lightning symbol. Power is supplied by a 15v battery (Mallory M 504 type or equivalent). To access the battery compartment, the terminal part of the foot must be moved downwards and the rear half of the shell retracted, completely extracting it.

Weight 7g., Battery and lamp excluded.

Dimensions: width 25mm .; height 70mm .; depth 40mm.

